



Scanwill Intensifier Solution Series SIS-52





Inlet flow: Min. 2 LPM to max. 20 LPM

Inlet pressure: Min. 10 bar to max. 200 bar*

* depending on the choosen ratio

Outlet Pressure: Variable 210 to 3,000 bar**

**depending on the choosen ratio and setting of the inlet pressure

Connections: G1/4" all ports, HP port with 120° cone sealing

Materials: Cast iron & steel

Available in stainless steel

Filtration requirement: Min. 10 micron nominal

200 micron strainers integrated

Connecting the SIS-52

Before installing make sure the surroundings and connecting parts are clean.

P: To be connected to pump supply T: To be connected to the tank line

Z: To be connected to the low pressure side of the cylinder

HP: To be connected to the high pressure side of the cylinder

The SIS-52 Range:

Ratio	Max. inlet pressure (bar)	Max. outlet pressure (bar)	Product code
7.0:1	30 - 200	210 - 1,400	SIS-52-7.0
10.0:1	30 - 200	300 - 2,000	SIS-52-10,0
13.0:1	30 - 200	390 - 2,600	SIS-52-13.0
16.0:1	30 - 188	480 - 3,000	SIS-52-16.0



